




Auto-Out® Microwave Specifications

FOR RESIDENTIAL COOKTOPS WITH OVER-THE-RANGE MICROWAVES



Product Name
Auto-Out® Microwave with Quick-Connect Bracket
Model Number
AOM-3
Application
Residential cooktops with over-the-range microwaves
Dimensions & Weight: One Unit
<ul style="list-style-type: none"> Weight: 1.3 lbs (without bracket) Height with Quick-Connect bracket: 3½" Height without Quick-Connect bracket: 2 ¾" Length: 11" Width: 3"
Product Highlights
<ul style="list-style-type: none"> Fire-suppressant device for cooktops with over-the-range microwaves 24-7 protection, no electrical or batteries required Affordable Helps protect property and residents
Fire suppression "canisters" per unit
One canister which protects the front and back burner
Quantity Needed
A pair for standard four-burner cooktops
Requirements
<ul style="list-style-type: none"> 15 - 27 inches from the cooktop surface to the bottom of microwave Minimum of 9.5 inches measuring from center of Left unit to center of Right unit after installed
Country of Manufacture
United States of America

Installation Method
<ul style="list-style-type: none"> Quick-Connect bracket - attaches to underside of microwave Wall-Mount bracket alternative - attaches to wall behind microwave
Track Record
Proven technology
Intended Use
Small residential cooking fires, including grease fires (not intended to suppress fires caused by "deep-fat" frying)
Certification & Testing
<ul style="list-style-type: none"> Tested by Southwest Research Institute® (SWRI), a Nationally Recognized Testing Laboratory (NRTL) Suppression agent subject to national lab test standards for "Dry Chemical Fire Extinguishers"
Product Life
<ul style="list-style-type: none"> 6 years from the date of manufacture One time use only
Activation Method
Triggered by the flames of the fire (neither steam, smoke, nor heat alone will actuate the device)
Primary Suppression Agent
Siliconized dry chemical powder (sodium bicarbonate base) subject to national lab test standards for "Dry Chemical Fire Extinguishers"
Dispersal Method
Non-pressurized, gravity aided device
Clean-Up
Use a damp towel to sweep up the environmentally-friendly powder